



Model EBT731 (Shown with standard and optional accessories)

# EBT Balometer® Capture Hood Model EBT731

The EBT731 Balometer™ Capture Hood is a multipurpose electronic air balancing instrument used for taking accurate, direct air volume measurements at diffusers and grilles. The corresponding detachable micromanometer can be used with an array of optional probes to enable various measurement applications. Compatible with LogDat™ Mobile Remote Reader Software and capture hood stand, the EBT731 maximizes worker productivity and efficiency—saving you valuable time on the jobsite for ultimate profitability.

# **Features and Benefits**

- Ergonomic, lightweight design enables easy one-person operation
- Automatic sensing and display of supply or return flows saves time on the job
- Back pressure compensation ensures accurate readings at high flow rates
- Detachable digital micromanometer provides additional measurement capability
- Multiple hood size options enable measurement of different outlet dimensions
- Compatible LogDat Mobile Remote Reader and Data Logger Software option simplifies documenting of results and emailing of reports
- Capture hood stand eliminates the need for ladders (reaching diffusers up to 15 ft. (4.5 m)

# **Applications**

- Test and balance contractors
- Commissioning agents
- Facilities managers
- Health and safety specialists
- Ventilation system installers





Model EBT730 (Micromanometer shown with standard and optional accessories )

# Detachable Micromanometer Model EBT730

As standard, the EBT731 Balometer Capture Hood includes a detachable EBT730 micromanometer—one of the most advanced, versatile, and easy to use micromanometers on the market today. The EBT730 features an auto-zeroing pressure sensor that increases measurement resolution and accuracy as well as integrates an intuitive menu structure to facilitate simple operation.

## **Features and Benefits**

- Accurate measurement of pressure, velocity and flow complies with industry standards
- Auto-zeroing pressure sensor reduces user-steps and saves time
- Automatic density correction increases reading accuracy
- Large, backlit graphic display offers easy-to-use interface
  - Up to five simultaneous measurements
  - On-screen messages and instructions
  - Multi-language capability
- Intuitive menu structure simplifies operation
- Bluetooth bi-directional communication eases data transfer and permits use of LogDat Mobile Remote Reader and Data Logger Software for Android devices
- Optional pitot, air flow (straight pitot), temperature/relative humidity, velocity matrix, or plug and play thermoanemometer probes enables use in multiple applications







# **Air Volume Instruments**

# Models EBT730 and EBT731

# Specifications

Micromanometer Model EBT730 and Capture Hood Model EBT731

**Velocity Range** 

Pitot probes 25 to 15,500 ft./min (0.125 to 78 m/s) 25 to 5,000 ft./min (0.125 to 25 m/s) Air flow probe Velocity matrix 25 to 2,500 ft./min (0.125 to 12.5 m/s) **Accuracy**  $\pm 3\%$  of reading  $\pm 7$  ft./min ( $\pm 0.04$  m/s) at

velocities >50 ft./min (>0.25 m/s)

Units ft./min. m/s Resolution 1 ft./min (0.01 m/s)

Pressure

**Differential pressure**  $\pm 15$  in. H<sub>2</sub>O ( $\pm 3735$  Pa); 150 in. H<sub>2</sub>O (37.5 kPa),

maximum safe operating pressure 15 to 40 in. Hg (356 to 1016 mm Hg) Absolute pressure

**Accuracy**  $\pm 2\%$  of reading  $\pm 0.0001$  in. H<sub>2</sub>O ( $\pm 0.025$  Pa) static and differential; ±2% of reading absolute

Units in. H<sub>2</sub>O, in. Hg, Pa, hPa, kPa, mm Hg,

cm  $H_{2}$ 0, cm  $H_{2}$ 0,

0.00001 in. H<sub>2</sub>O (0.001 Pa) static and Resolution

differential; 0.01 in. Hg (1 mm Hg) absolute

Volume

Range 25 to 2,500 ft.3/min (42 to 4250 m3/h) capture hood, supply and return

±3% of reading ±7 ft.3/min (±12 m3/h) at **Accuracy** 

flows >50 ft.3/min (>85 m3/h) Units ft.3/min, m3/h, m3/min, l/s

Resolution 1 ft.3/min (1 m3/h)

RH

Range 5 to 95% RH (temperature/RH probe)

Accuracy ±3% RH Resolution 0.1% RH

**Temperature** 

Sensor in base 40 to 140°F (4.4 to 60°C) Temperature/RH probe 14 to 140°F (-10 to 60°C)

Accuracy ±0.5°F (±0.3°C) °F, °C Units Resolution 0.1°F (0.1°C)

Instrument Temperature Range

**Operating** 40 to 140°F (4.4 to 60°C) -4 to 160°F (-20 to 71°C) Storage

Statistics

min, max, average and sun

Data Storage

26,500 samples, time and date stamped

Logging Interval

User selectable

Response Time

2 to 8 seconds, differential pressure sensor

Dimensions (micromanometer only)

7.4 in. x 4.5 in. x 2.3 in. (18.8 cm x 11.4 cm x 5.8 cm)

**Pressure Connection** 

1/4 in. (6.35 mm) OD straight ports with barbed ends for use with <sup>3</sup>/<sub>16</sub> in. (4.76 mm) ID flexible tubing

Weight with Batteries

17 oz. (0.5 kg) **EBT730 EBT731** 7.4 lb. (3.4 kg)

**Power Requirements** 

Four AA-size cells or AC adapter

#### Standard Accessories

Capture Hood Model EBT731

Micromanometer Model EBT730 Micromanometer carry case

- Wheeled luggage-style carrying case
- 2 ft. x 2 ft. (610 mm x 610 mm) air capture hood/frame/base
- Detachable micromanometer
- AA rechargeable NiMH batteries (qty = 4)
- Multi-country AC adapter
- 18 in. (46 cm) pitot probe
- Static pressure probes (qty = 2)
- 16 ft. (4.8 m) neoprene tubing
- Down-loading software
- USB interface cable
- NIST-traceable calibration certificate
- Product manual

- AA rechargeable NiMH batteries (qty = 4)
- Multi-country AC adapter
- 18 in. (46 cm) pitot probe
- Static pressure probes (qty = 2)
- 16 ft. (4.8 m) neoprene tubing
- Down-loading software
- USB interface cable
- NIST-traceable calibration certificate
- Product manual

# **Air Volume Instruments**

# Models EBT730 and EBT731

# **Recommended Optional Accessories**

#### **Hood Kits**

**801097 (standard)** 2 ft. x 2 ft. (610 mm x 610 mm) 801200 1 ft. x 4 ft. (305 mm x 1220 mm) 801201 2 ft. x 4 ft. (610 mm x 1220 mm) 1 ft. x 5 ft. (305 mm x 1525 mm) 801202 801203 3 ft. x 3 ft. (915 mm x 915 mm) 16 in. x 16 in. (406 mm x 406 mm) 801209 5.25 in. x 4 ft. (133 mm x 1220 mm) 801210 28 in. x 28 in. (710 mm x 710 mm) 801211 28 in. x 50 in. (710 mm x 1270 mm) 801212 801204 (BSC\*) 8 in. x 22 in. (205 mm x 560 mm) 10 in. x 22 in. (255 mm x 560 mm) 801205 (BSC\*)

\*The BSC hood kits are used to certify Class II bio-safety cabinets by taking direct in-flow measurements for NSF compliance.

#### **Duct Plugs**

**634650002** 3/8 in. (9.5 mm) diameter - 1000 pieces **634650003** 3/8 in. (9.5 mm) diameter - 5000 pieces

#### Printer

**8934** Wireless Bluetooth printer

#### LogDat™ Mobile Remote Reader Software

LogDat™ Mobile

Remote reader and data logger Android™ Software App available via Google Play™



#### Capture Hood Stand



Extends up to 15 ft. to take readings from ceiling diffuser without the use of a ladder. Capture hood is secured onto quad bracket and two extension pole sections can be raised to desired height and locked in place. Hood stand uses wheels for ease of movement and portability.

Specifications subject to change without notice.
TSI, the TSI logo, Alnor, LogDat and Balometer are trademarks of TSI Incorporated.
AiRNAB is a trademark of AIRNAB LLC.
Android and Google Play are trademarks of Google Inc.

#### **Probes**

#### Airflow Probe 800187

Straight air flow probe, 18 in. (46 cm). Used to perform a duct traverse and to measure face velocity measurements. Ideal for small diameter ductwork.

#### Temperature and Humidity Probe 800220

Telescopic temperature and humidity probe, extends 9-39 in. (230-990 mm). Used for measuring inside of duct work. Can be inserted into a standard 5/16 in. (8 mm) diameter hole typically use for pitot traverses with the ability to calculate wet bulb and dewpoint temperatures.

#### Thermoanemometer Air Velocity Probes

#### Model 960

Straight air velocity and temperature probe

#### Model 962

Articulating air velocity and temperature probe

#### Model 964

Straight air velocity, temperature and humidity probe with ability to calculate wet bulb and dewpoint temperature

### Model 966

Articulating air velocity, temperature and humidity probe with ability to calculate wet bulb and dewpoint temperature

# Velocity Matrix 801090 ·····

16 point Telescopic Velocity Matrix.

Used for measuring face velocities of HEPA filters, chemical fume hood, laminar flow benches, filter banks, kitchen exhausts and other applications

where a large surface area needs to be measured. Grid covers one square foot area and averages the air velocity while minimizing the effects of turbulence to produce a stale reading.



## Pitot Probes ······

634634000	5/16-12 in. (8 mm – 30 cm) diameter
634634001	5/16-18 in. (8 mm - 46 cm) diameter
634634002	5/16-24 in. (8 mm - 61 cm) diameter
634634003	5/16-36 in. (8 mm - 91 cm) diameter
634634005	5/16-60 in. (8 mm - 152 cm) diameter

Alnor Products, TSI Incorporated - 500 Cardigan Road Shoreview, MN 55126-3996 USA USA Tel: +1 800 424 7427 E-mail: customerservice@alnor.com





Contact your local Alnor Distributor or visit our website www.alnor.com for more detailed specifications.

Printed in U.S.A.