

# Model FD 115 | Drying and heating chambers with forced convection

A BINDER FD series Avantgarde. Line heating oven is always used when fast drying and sterilization is required. Thanks to its fully homogeneous temperature distribution, quick dynamics and powerful fan, this heating oven saves valuable time.

## **BENEFITS**

- · Best energy efficiency on the market
- Excellent temporal and spatial temperature accuracy
- · USB connection for recording data
- Temperature range up to 300 °C



Model 115

## MAIN FEATURES

- Temperature range: ambient temperature plus 10 °C to 300 °C
- Up to 30% lower energy consumption compared to conventional units on the market
- High temperature accuracy thanks to APT.line™ technology
- Forced convection
- · Controller with LCD display
- · Electromechanical control of the exhaust air flap

- · 2 chrome-plated racks
- · Stackable
- Class 2 integrated independent adjustable temperature safety device (DIN 12880) with visual alarm
- Ergonomic handle design
- · USB port for recording data

## ORDERING INFORMATION

Interior volume [cu.ft.]	Voltage	Option model	Version	ArtNo.
4.1	230 V 1~ 50/60 Hz	Standard	FD115-230V	9010-0305
	120 V 1~ 60 Hz	Standard	FD115UL-120V	9010-0306




## **TECHNICAL DATA**

Description	FD115-230V <sup>1</sup>	FD115UL-120V <sup>1</sup>
Article Number	9010-0305	9010-0306
Performance Data Temperature		
Temperature range 10 °C above ambient temperature to [°C]	300	300
Temperature variation at 150 °C [± K]	1.7	1.7
Temperature fluctuation at 150 °C [± K]	0.3	0.3
Heating-up time to 150 °C [min]	18	18
Recovery time after 30 seconds door open at 150 °C [min]	4	4
Air change data		
Air change (approx.) at 100 °C [x/h]	32	32
Electrical data		
Rated Voltage [V]	230	120
Power frequency [Hz]	50/60	60
Nominal power [kW]	1.3	1.4
Unit fuse [A]	6.3	12.5
Phase (Nominal voltage)	1~	1~
Measures		
Interior volume [cu.ft.]	4.1	4.1
Net weight of the unit (empty) [lbs]	126	126
Permitted load [lbs]	331	331
Load per rack [lbs]	66	66
Wall clearance back [in]	6.3	6.3
Wall clearance sidewise [in]	3.94	3.94
Internal Dimensions		
Width [in]	21.67	21.67
Height [in]	21.67	21.67
Depth [in]	15.17	15.17
Doors		
Unit doors	1	1
Housing dimensions not incl. fittings and connections		
Width net [in]	27.97	27.97
Height net [in]	28.96	28.96
Depth net [in]	23.84	23.84
Environment-specific data		
Energy consumption at 150 °C [Wh/h]	340	340
Sound-pressure level [dB(A)]	43	43
Fixtures		
Number of shelves (std./max.)	2/5	2/5

<sup>1</sup> All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.



## DIMENSIONS INCL. FITTINGS AND CONNECTIONS [MM]



## **OPTIONS**

Designation	Description	*	ArtNo.
	left		
	10 mm	01	8012-1276
	30 mm	01	8012-1016
	50 mm	01	8012-1020
	100 mm	01	8012-1027
	right		
	10 mm	01	8012-1269
Access port with silicone plug	30 mm	01	8012-1015
piug	50 mm	01	8012-1019
	100 mm	01	8012-1028
	top		
	10 mm	01	8012-1263
	30 mm	01	8012-1364
	50 mm	01	8012-1380
	100 mm	01, 10	8012-1671
Alarm function for overheating	Switchable acoustic alarm, with adjustable limit value on the independent temperature safety device	-	8012-1636
Analog output 4-20 mA	for temperature values (output not adjustable)	02	8012-1624
Calibration certificate, expanded	for temperature; for extending the measurement in center of chamber to include another test temperature	-	8012-1116
	for temperature, measurement in center of chamber at specified temperature	-	8012-1135
Calibration certificate,	temperature measurement incl. certificate and 27 measuring points at specified temperature	-	8012-1594
temperature	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	_	8012-1573
	temperature measurement incl. certificate, 9 measuring points at specified temperature	_	8012-1552
Class 3.1 independent temperature safety device	with visual alarm (DIN 12880)	04, 12	8012-1643
Clock	battery-backed	-	8012-1641
Door gasket	made of FKM, silicone-free	03	8012-1650
Door lock	lockable door handle	-	8012-1665
Ethernet interface	for Multi Management Software APT-COM™	-	8012-0988
Gas-tight option model	Incl. additional measures for the greatest possible impermeability to gas; not in conjunction with access port or interior lighting option	09	8012-1685
Heating output,	For faster heating up time and improved recovery time; max. 300 °C; not in conjunction with load management option		
reinforced	120/230 V option model	-	8012-1057
HEPA air filter	On fresh air supply for unit; filter classification H14 (acc. to. EN 1822-1:2009, > 99.995% at 0.3 µm)	_	8012-1051
Inert gas connection	With gas inlet and outlet, Ø 10 mm, incl. additional measures for the greatest possible impermeability to gas; not in conjunction with access port or interior lighting option	-	8012-1691
Inner chamber, reinforced	max. total load 170 kg	-	8012-1054

<sup>\*</sup> Notes > See last page



Designation	Description	*	ArtNo.
	with 15 W light bulb		,
Interior lighting	120 V option model	-	8012-1632
	230/240 V option model	-	8012-1628
Measurement of air exchange rate	in accordance with ASTM D5374, definition and protocol according to ambient temperature	-	8012-1195
Pt 100 temperature sensor	additional flexible Pt 100, interior, for displaying the temperature on the unit display	-	8012-1620
Viewing window and interior lighting	viewing window (triple insulating glass) in door, 370 x 370 mm, and 15 W interior		
	120 V option model	-	8012-1706
	230 V option model	_	8012-1704

<sup>\*</sup> Notes > See last page

## **ACCESSORIES**

Designation	Description	*	ArtNo.
APT-COM™ 4 BASIC-	for simple logging and documentation requirements with up to 5 networked units.		
Edition	version 4, BASIC edition	19	9053-0039
APT-COM™ 4 GLP- Edition	for working under GLP-compliant conditions. Measured values are documented in a tamper-proof way in line with the requirements of FDA Regulation 21 CFR 11.		
	version 4, GLP edition	19	9053-0042
APT-COM™ 4	convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.		
PROFESSIONAL- Edition	version 4, PROFESSIONAL edition	19	9053-0040
Data Logger Kit	T 350: For continuous temperature logging from 0 °C to 350 °C; kit includes 1 data logger, Pt 100 sensor with 2 m extension cable and 1 magnetic fixture for mounting to the BINDER unit	19	8012-0714
Data Logger Software	LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable)		8012-0821
	with lid made from 18/8 stainless steel, stackable, dimensions: 230 x 133 x 45 mm	-	4022-0123
Instrument tray	with lid made from 18/8 stainless steel, stackable, dimensions: 315 x 215 x 60 mm	-	4022-0124
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	-	1002-0016
	IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO <sub>2</sub> , O <sub>2</sub> , pressure, depending on unit		
	Digital in PDF format	-	7057-0001
O 1:5: 1: 1	Hard copy inside folder	-	7007-0001
Qualification documents	IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO <sub>2</sub> , O <sub>2</sub> – or pressure, depending on unit		
	Digital in PDF format	-	7057-0005
	Hard copy inside folder	-	7007-0005
Dools	chrome plated	-	6004-0167
Rack	stainless steel	-	6004-0151
Rack, heavy load	Stainless steel, max. load per rack 70 kg	-	6004-0199
Rubber pads	set anti-slip feet	-	8012-1887
Shelf, perforated	Stainless steel	-	6004-0183
Table on castors	stable cart, casters with locking brakes, dimensions: W 1,000 x D 800 x H 780 mm		9051-0018

<sup>\*</sup> Notes > See last page



## **SERVICES**

Designation	Description	*	ArtNo.
Installation services			
Unit installation	Unpacking and setting up of unit, connecting to existing connections, and checking function	13, 18	DL10-0100
Unit instructions	Unit function instructions for operation and programming of the controller	18	DL10-050
Preventive maintenance			
Maintenance	Functional testing of all electrical and mechanical components, short calibration, documentation in the maintenance schedule	14, 18	DL20-0200
Calibration services			
Measurement of air exchange rate	including certificate (in accordance with ASTM D5374)	14, 16, 17, 18	DL33-000
Temperature calibration	Expansion – including certificate, each additional measuring point in center of chamber at specified test temperature	14, 16, 17, 18	DL30-010
	Temperature calibration with 1 measuring point in center of chamber at a specified test temperature, including certificate	14, 16, 17, 18	DL30-010
Temperature measurement, 18 measuring points	Temperature measurement with 18 measuring points at a specified test temperature, including certificate	14, 16, 17, 18	DL30-011
Temperature measurement, 27 measuring points	Temperature measurement with 27 measuring points at a specified test temperature, including certificate	14, 16, 17, 18	DL30-012
Temperature measurement, 9 measuring points	Temperature measurement with 9 measuring points at a specified test temperature, including certificate	14, 16, 17, 18	DL30-010
Validation services			
Execution of IQ/OQ	Execution of IQ/OQ in accordance with qualification folder	15, 18	DL40-010
Execution of IQ/OQ/PQ	Execution of IQ/OQ/PQ in accordance with qualification folder	15, 18	DL44-050
Warranty service			
Warranty extension from 2 to 3 years	The warranty is extended from 2 to 3 years from the delivery date, wear parts are excluded	-	DL00-304
Warranty extension from 2 to 5 years	The warranty is extended from 2 to 5 years from the delivery date, wear parts are excluded	-	DL00-304

<sup>\*</sup> Notes > See last page



#### **NOTES**

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.
- 02 UL mark is not granted when this option is used.
- Heat resistant only to max. 200 °C. 03
- Only available on units rated for 230 V.
- The additional heat input may affect the temperature behavior.
- Not in conjunction with the optional access port, door with window and interior lighting.
- 10 Not available on 23-liter units.
- Not available on 23- or 53-liter units.

  Only available on units rated for 230 V or 400 V. 11 12
- 13 Installation and connections take place at unit location; transport within the company only upon consultation.
- We recommend a BINDER service contract to cover unit inspections, calibrations and validations.
- OQ according to Yellow Paper = completed factory validation documentation of all OQ checklists.
- Sensor calibration is performed in an accredited calibration laboratory.
- Calibration is performed according to the BINDER factory standard. 17
- Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not 18 include a country-specific added fee (available on request).
- For additional accessories, refer to the Process documentation chapter.

BINDER GmbH Tuttlingen, Germany TEL +49 7462 2005 0 FAX +49 7462 2005 100 info@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd. Kowloon, Hong Kong, P.R. China TEL +852 39070500 FAX +852 39070507 asia@binder-world.com www.binder-world.com

**BINDER Environmental Testing** Equipment (Shanghai) Co., Ltd. Shanghai, P.R. China TEL +86 21 685 808 25 FAX +86 21 685 808 29 china@binder-world.com www.binder-world.com

Representative Office for CIS Moscow. Russia TEL +7 495 988 15 16 FAX +7 495 988 15 17 russia@binder-world.com www.binder-world.com

BINDER Inc. Bohemia, NY, USA TEL +1 631 224 4340 FAX +1 631 224 4354 usa@binder-world.com www.binder-world.us